

Hook trolley 20 pairs of hooks

P/N: 7506173 | HAW 605/620/1620 1/4HP 4Ko

HUPFER
we make work flow

Technical data



Weight:	17 kg
Width:	605 mm
Depth:	620 mm
Height:	1620 mm

Similar to illustration, technical modifications reserved. Without decoration.

The hook trolley for operating theatre shoes is used to transport and store operating theatre shoes in shoe baskets.

The stainless steel hook trolley for 20 pairs of shoes is used for convenient transport and user-friendly organisation of operating theatre shoes in baskets attached to it. The Hupfer hook trolley ensures easy handling and efficient transport processes in any medical working environment. The all-round welded frame made of stainless steel square tube with curved upper corners is particularly torsion-resistant and robust. The frame also serves as a push bar. Firmly welded pairs of hooks make it easy to attach the appropriate accessories. Thus equipped, the hook trolley allows quick access and a clear overview of the supplies to be provided. The high-quality design guarantees optimum hygiene for demanding environments. The base of the trolley made of square tube with rounded corners and four swivel castors with two locks ensures smooth movement and precise manoeuvring. The antistatic tyres prevent electrostatic charging and provide effective protection against potential sparks. Hook trolley with single side loading with 4 holders for baskets.

- Open design for fast access and user-friendly organisation
- Firmly welded pairs of hooks allow the accessories to be easily attached in the configuration required
- High-quality design guarantees easy cleaning and optimum hygiene
- Swivel castors ensure smooth movement and precise manoeuvring
- Locks guarantee safe movement and immobilisation

Time and date of the request: 29.04.2026, 08:36:02 *All information / dimensions are approximate, technical changes reserved. © Hupfer*

Hook trolley 20 pairs of hooks

P/N: 7506173 | HAW 605/620/1620 1/4HP 4Ko

HUPFER
we make work flow

- Antistatic tyres prevent electrostatic charging and protect highly sensitive equipment

Time and date of the request:
29.04.2026, 08:36:02

All information / dimensions are approximate, technical changes reserved. © Hupfer